

MULTI ATTACHMENT MINISHAKER

Ms 602 Minishaker

Universal, sized shaker . with and orbit of 4.5 milimeter and a speed range of 0 - 2500 rpm the MS 602 is suitable for all small vessels.

- Electronic speed control
- Convenient handing provided by control console facing the operator
- Flat construction
- Attractive designn
- Can either be Operated continusly or with automatic starter,wich is triggered by pressing the attachment
- Electronic speed control

شیکر لوله و شیکر الایزا MS602 - MS601

- دستگاههای مینی شیکر ساخت شرکت فاطرالکترونیک با طراحی بسیار زیبا کاربرد آسان در دو مدل ارائه می گردند.
- مدل MS 602 با یک آداپتور و بعنوان شیکر ورتکس جهت استفاده در آزمایشگاه قابل استفاده می باشد.
 - سه حالت کار دستگاه: ۱- دایم روشن ۲- روشن با فشار لوله روی آداپتور ۳- قابلیت تنظیم سرعت چرخش و شیک کردن در حالت اتوماتیک بوسیله ولوم کنترل
 - مدل MS 601 با سه آداپتور و بعنوان شیکر ورتکس و شیکر الایزا با کاربرد گسترده تر جهت استفاده در آزمایشگاه قابل استفاده می باشد.
 - میزان حرکت چرخشی آداپتور شیکر ۴,۵ میلیمتر
 - سرعت حرکت چرخشی دستگاه ۲۵۰۰ دور در دقیقه



MS 602



MS601 MINISHAKER

Same features as MS 602, additionally suitable for work with a microtiter plate. larg selection of attachments.



MS 601

MODEL No.	Control	Speed	No. of Adapter	Movement mm	power Rating W	Permissible ON time	Permissible Shaking Weight	Dimention mm	Weight - Kg
MS 602	Electronic	0 - 2500	1	4.5	18	%100	0.5 Kg	13x225x750	3.5
MS 601	Electronic	0 - 2500	3	4.5	18	%100	0.5 Kg	13x225x750	3.5